

# GO Regulator

# **BP-60 Series**

High Pressure Back Pressure Regulators

### Introduction

The BP-60 Series is the counterpart of the PR-50 pressure reducing series for systems that are higher in pressure and low to moderate flows. This regulator has a diaphragm for maximum sensitivity in providing relief at high pressures. The PTFE stainless seat assembly provides good shutoff in most applications. For economy purposes the cap assembly and knob are of aluminum construction as in the PR-50 companion unit. Good sensitivity and a wide selection of control ranges make this regulator an excellent selection in many research and pilot plant facilities.



### **Typical Applications**

- Sampling Systems
- Pilot plants
- Research labs

#### **Technical Data**

CONSTRUCTION	316L stainless steel or brass (alloy 360) MONEL® and HASTELLOY® C-276 (optional)			
ADJUSTABLE PRESSURE CONTROL RANGES	0-500, 0-1000 and 0-2000 psig			
OPERATING TEMPERATURE	-40° F to +350° F (-40° C to +175° C)			
C <sub>V</sub> COEFFICIENT	0.04			
INLET/OUTLET CONNECTIONS	1/4" FNPT			

#### Features & Benefits

- Designed for moderate flow applications
- Diaphragm sensing with nylon, PTFE or stainless steel diaphragm
- Bubble tight shutoff

#### **Options**

- Various other Cv's available 0.005, 0.01, 0.025, 0.09
- Panel mounting
- 3/8" FNPT connections

# **High Pressure Back Pressure Regulators**

### **Maximum Temperature and Control Pressures**

#### **Nylon Diaphragm Backing**

SEAT MATERIAL	MAXIMUM TEMPERATURE	@	MAXIMUM CONTROL RANGE
Tefzel®	175° F (80° C)	@	1000 psig (6.89 MPa)
PTFE	175° F (80° C)	@	1000 psig (6.89 MPa)
Polyimide	175° F (80° C)	@	2000 psig (13.76 MPa)
PEEK™	175° F (80° C)	@	2000 psig (13.76 MPa)
CF PTFE	175° F (80° C)	@	1000 psig (6.89 MPa)

#### PTFE Diaphragm Backing

	SEAT MATERIAL	MAXIMUM TEMPERATURE	@	MAXIMUM CONTROL RANGE
	Tefzel®	175° F (80° C)	@	2000 psig (13.76 MPa)
	PTFE	175° F (80° C)	@	2000 psig (13.76 MPa)
	Polyimide	350° F (176° C)	@	2000 psig (13.76 MPa)
	PEEK™	350° F (176° C)	@	2000 psig (13.76 MPa)
	CF PTFE	175° F (80° C)	@	1000 psig (6.89 MPa)

### How to Order

To Order, contact your local Distributor Link below: www.goreg.com/distributor/index.htm

Verify that your chosen part number is valid using the GO Wizards at www.goreg.com/products/matrix/index.htm

For additional configurations, consult the factory. Standard items in bold.

# BP60 - 1

**Body Material** -

- 1 316L stainless steel
- 2 Brass
- 4 MONEL®
- 6 HASTELLOY® C-276

Port Configuration -

A Standard (body "A")

See pg. 28 for port locations.

Process Port Types -

- 1 ¼" FNPT (¼" FNPT gauge ports)
- 4 3/8" FNPT (1/4" FNPT gauge ports)

Cavity Finish -

- 1 < 25 Ra
- **5** < 25 Ra with 10-32 mounting holes

Actuator Material -

- A Tefzel®
- **B** CF PTFE
- **C** Polyimide
- I PTFE
- Q PEEK™

NOTE: Contact the factory for any additional requirements.

For flow curve charts, visit www.goreg.com.

g	U	0	п	S		
•					_	

- EB33 (oxygen cleaning)
  - EB5 cleaning
- Helium leak test
- Pressure test certificate Certificate of Conformity
- **CMTR**

Cap Assembly

- 1 Standard, aluminum
- 4 Panel mount, aluminum
- 5 Captured vent, aluminum
- 6 Captured vent, panel mount, aluminum
- 7 Captured vent, stainless steel
- F Captured vent, stainless steel

Diaphragm Facing/Backing Material

	FACING	BACKING	O-RING	ACTUATOR
1	SS	Nylon	Viton®	SS
2	None	Nylon	PTFE	SS
3	Polymide	Nylon	Viton®	SS
4	SS	Nylon	PTFE	SS
5	None	Nylon	PTFE	MONEL®
6	Polymide	Nylon	PTFE	SS
7	INCONEL®	Nylon	Viton®	MONEL®
8	INCONEL®	Nylon	PTFE	MONEL®
0	HASTELLOY® C-276	Nylon	PTFE	HASTELLOY® C-276
A	HASTELLOY® C-276	Nylon	Viton®	HASTELLOY® C-276
В	None	Nylon	Viton®	MONEL®
Н	None	Nylon	Viton®	SS
Q	SS	PTFE	PTFE	SS
S	SS	PTFE	PTFE/Kalrez®	SS (max. 450° F)
T	SS	PTFE	Kalrez®	SS (max. 570° F)
٧	INCONEL®	PTFE	PTFE	MONEL®
W	HASTELLOY® C-276	PTFE	PTFE	HASTELLOY® C-276

Diaphragm Type

1 Standard diaphragm

Control Range J 0-500 psig

**K** 0–1000 psig **L** 0–2000 psig

Flow Coefficient (C<sub>v</sub>) C 0.025

- E 0.04
- **G** 0.09
- 0.005 0.01