

GO Regulator


HPR-2 Series

Electrically Heated Regulators

Introduction

The HPR-2 Series heated pressure regulator is designed to supply heat to samples entering instrumentation systems. It can be used to preheat liquids, to prevent condensation of gases or to vaporize liquids prior to gas analysis.

The modular design of the HPR-2 consists of heat exchanger and pressure control sections. The pressure control section is patterned after the time proven design of the PR-1 pressure reducing regulator and provides the same excellent outlet pressure stability. The heat exchanger section is made up of a body and heat exchange element. The heat exchange element uses GO Regulator's



unique spiral wrapped screen as the heat exchange surface. This screen has up to 100 square inches of heat transfer area and precise design forces all sample flow to pass through the element.

The HPR-2 Series of vaporizing pressure reducing regulators are both CSA and ATEX approved. The electrical components of this unit are securely housed in a Class A, B, C, D condulet assuring that there is always an adequate flame path between the environment and the controller. Safety considerations can be further enhanced by using the optional TCO (Thermal Cut Out) heater cartridge and proportional controller. These features enable the unit to boast a T3 rating with 150 watts of power.

Typical Applications

Analytical process sample conditioning systems:

- Petrochemical refineries
- Chemical production facilities
- Pilot plants (chemical & petrochemical)
- LNG loading and off-loading points
- Natural gas pipeline sampling

Technical Data

CONSTRUCTION	316L stainless steel					
OUTLET PRESSURES	0-10, 0-25, 0-50, 0-100, 0-250, 0-500 0-750, and 0-1000 psig					
INLET PRESSURE	up to 6000 psig at 380° F (193° C)					
HEATING CAPACITY RANGES (IN WATTS)	40, 50, 100, 150, 200 and 250					
C _V COEFFICIENTS	0.06, 0.025, 0.2					
CERTIFICATIONS	CSA certification # LR-82566-5 ATEX Directive 94/9/EC Certification # TRL03ATEX11001X					


Features & Benefits

- Optional HASTELLOY® C and MONEL®
- Electropolished body with better than 25 Ra finish in diaphragm cavity for an optimal sealing surface
- Bubble-tight shutoff
- Modular pressure control and heat exchanger assemblies for easy maintenance
- Unique spiral wrapped heat exchange element provides up to 100 square inches of heat transfer area.
- Available in 120VAC or 240VAC
- Optional TCO heating cartridge and proportional controller
- INCONEL® diaphragm standard

sure regulators

How to Order

Standard items in bold



Maximum Temperature & Operating Inlet Pressures

HPR-2 Electric 2-piece Assembly

(Heater block and regulator body separate)

•			•
SEAT MATERIAL	MAXIMUM PRESSURE	@	MAXIMUM OPERATING INLET PRESSURE
	Up to 175° F (80° C)	@	3600 psig (24.82 MPa)
Tefzel®	176° F to 300° F (80° C to 148° C)	@	1000 psig (6.90 MPa)
& CF PTFE	301° F to 380° F (148° C to 193° C)	@	400 psig (2.76 MPa)
PCTFE (formerly Kel-F®)	Up to 380° F (193° C)	@	3600 psig (24.82 MPa)
PEEK™	Up to 380° F (193° C)	@	3600 psig (24.82 MPa)

HPR-2 Electric 1-piece Assembly

(Integral heater block and regulator)

	SEAT MATERIAL	MAXIMUM PRESSURE	@	MAXIMUM OPERATING INLET PRESSURE
	Tefzel® & CF PTFE -	Up to 175° F (80° C)	@	3600 psig (24.82 MPa)
		176° F to 300° F	@	1000 psig (6.90 MPa)
		(80° C to 148° C)	@	
		301° F to 380° F	@	400 psig (2.76 MPa)
		(148° C to 193° C)		
	PCTFE (formerly Kel-F®)	Up to 380° F (193° C)	@	3600 psig (24.82 MPa)
	PEEK™	Up to 380° F (193° C)	@	6000 psig (24.82 MPa)